

VIAVI

T-BERD/MTS-6000A and -8000 Platforms

8100-Series CWDM OTDR EVO Modules

The VIAVI Solutions CWDM module, part of the 8100-Series OTDR EVO family can connect anywhere on the fiber to characterize CWDM networks for commissioning, network upgrades, and troubleshooting with the insurance of workflow optimization and accurate fiber-link fingerprinting.

The optical performance of the CWDM module, combined with the T-BERD/MTS platform's suite of testing features, ensures that testing jobs are performed right the first time to successfully deploy and maintain metro- and mobile-backhaul networks.

Testing features include:

- Automatic multitest configuration
- Summary results table with pass/fail analysis
- Linear trace interpretation with SLM (optional)
- Fast-Report — onboard report generation

Platform Compatibility

T-BERD/MTS-6000A




Compact multilayer platform for network installation and maintenance

T-BERD/MTS-8000 (V2)



Scalable platform for multiple-layer and multiple-protocol testing



Key Benefits

- Characterize fiber links with exact CWDM wavelengths per ITU-T G.694.2
- Test through CWDM multiplexers, optical add/drop multiplexers (OADM), and demultiplexers with central wavelength control
- Troubleshoot live networks with in-service testing feature
- Verify end-to-end continuity using the continuous wave source
- Eliminate OTDR interpretation errors with Smart Link Mapper (SLM) without compromising on test time

Key Features

- Optimized dynamic range to test through mux, OADM, and demux
- Headend/central-office testing with sequenced short acquisition
- Integrated continuous-wave light source with modulation capability
- Instantaneous traffic detection
- Central wavelength control for accurate mux/demux loss measurement

Applications

- Test any CWDM network configuration
- Qualify fiber links during CWDM installation
- Wavelength provisioning—test new wavelength routes without disrupting traffic on active channels
- In-service troubleshooting—pinpoint the nature of a fault and its exact location

Specifications (Typical at 25°C)

General	
Weight	approx. 500 g (1.1 lb)
Dimensions (W x H x D)	213 x 124 x 32 mm (8.38 x 4.88 x 1.26 in)
Laser safety class (21 CFR)	Class 1
Distance units	Kilometer, meter, feet, and miles
Group index range	1.30000 to 1.70000 in 0.00001 steps
Number of data points	Up to 256,000 data points
Storage	Bellcore/Telcordia compatible Version 1.1 and Version 2.0

Distance Measurements	
Mode	Automatic or dual cursor
Display range	From 0.5 to 320 km
Display resolution	1 cm
Cursor resolution	From 1 cm
Sampling resolution	From 4 cm
Accuracy	$\pm 0.75 \text{ m} \pm \text{sampling resolution} \pm 1.10^{-5} \times \text{distance}$ (excluding group index uncertainties)

Attenuation Measurements	
Mode	Automatic, manual, 2-point, 5-point, and LSA
Display range	1.25 to 55 dB
Display resolution	0.001 dB
Cursor resolution	From 0.001 dB
Linearity	$\pm 0.03 \text{ dB/dB}$
Threshold	0.01 to 5.99 dB in 0.01 dB steps

Reflectance/ORL Measurements	
Mode	Automatic or manual
Reflectance accuracy	$\pm 2 \text{ dB}$
Display resolution	0.01 dB
Threshold	-11 to -99 dB in 1 dB steps

OTDR Modules	8100 CWDM1E	8100 CWDM2E	8100 CWDM3E	8100 CWDM4E	8100 CWDM5E
Wavelength ¹	1551/1571/1591/1611 $\pm 3 \text{ nm}$	1471/1491/1511/1531 $\pm 3 \text{ nm}$	1431/1451 $\pm 3 \text{ nm}$	1351/1371/1391/1411 $\pm 3 \text{ nm}$	1271/1291/1311/1331 $\pm 3 \text{ nm}$
Dynamic range ²	42 dB	42 dB	42 dB	42 dB	42 dB
Pulse width	3 ns to 20 μs	3 ns to 20 μs	3 ns to 20 μs	3 ns to 20 μs	3 ns to 20 μs
Event dead zone ³	0.8 m	0.8 m	0.8 m	0.8 m	0.8 m
Attenuation dead zone ⁴	4.5 m	4.5 m	4.5 m	4.5 m	4.5 m
Continuous wave light source Wavelengths Output power Stability Operating modes ⁵	All listed above 0 dBm < $\pm 0.1 \text{ dB}$ at 25°C, over 1 hour CW, 270 Hz, 330 Hz, 1 kHz, 2 kHz				
Automatic traffic detection	Yes				

*Time-based controller/clock accuracy

1. Measured at 10 μs
2. The one-way difference between the extrapolated backscattering level at the start of the fiber and the RMS noise level after 3 minutes averaging using the largest pulse width
3. Measured at $\pm 1.5 \text{ dB}$ down from the peak of an unsaturated reflective event using the shortest pulse width
4. Measured at $\pm 0.5 \text{ dB}$ from the linear regression using a FC/PC reflectance and using the shortest pulse width
5. Subtract 3 dB when used in modulation mode (270/330/1k/2k Hz)

Ordering Information

Description	Part Number
8100-Series CWDM OTDR EVO Modules	
CWDM OTDR 1551/1571/1591/1611 nm	E8140OTDRCWDM1E
CWDM OTDR 1471/1491/1511/1531 nm	E8140OTDRCWDM2E
CWDM OTDR 1431/1451 nm	E8120CWDMOTDR3E
CWDM OTDR 1351/1371/1391/1411 nm	E8140CWDMOTDR4E
CWDM OTDR 1271/1281/1311/1331 nm	E8140CWDMOTDR5E

Description	Part Number
Interchangeable Optical Connectors	
Straight connectors	EUNIPCFC, EUNIPCSC, EUNIPCST, EUNIPCDIN, EUNIPCLC
8° angled connectors	EUNIAPCFC, EUNIAPCSC, EUNIAPCDIN, ENIAPCLC

For more information about the T-BERD/MTS-6000A and -8000 test platforms, refer to their respective data sheets.

VIAVI Care Support Plans

Increase your productivity for up to 5 years with optional VIAVI Care Support Plans:

- Maximize your time with on-demand training, priority technical application support and rapid service.
- Maintain your equipment for peak performance at a low, predictable cost.

Features

*5-year plans only

Plan	Objective	Technical Assistance	Factory Repair	Priority Service	Self-paced Training	5 Year Battery and Bag Coverage	Factory Calibration
 BronzeCare	Technician Efficiency	Premium	✓	✓	✓		
 SilverCare	Maintenance & Measurement Accuracy	Premium	✓	✓	✓	✓*	✓

